

## **AV-55 HEPA Air Operated Industrial HEPA Vacuums**





---

## Industrial Vacuums for Hazardous Materials

### Compressed Air Industrial **HEPA<sup>Plus</sup>** Vacuums

PrestiVac Compressed Air Industrial **HEPA<sup>Plus</sup>** Vacuums are specifically designed to safely vacuum toxic, nuisance, hazardous dusts. Absolute **HEPA<sup>Plus</sup>** filtration with an efficiency of 99.995% @ 0.2 micron captures all of the hazardous dust and ensures the exhaust air is clean, keeping the operator and the environment safe from exposure and contamination.

#### Features:

- Powerful Suction - High Performance
- All Stainless steel construction makes it a solid unit that is easy to clean and sterilize

- Automatic Filter Shaker
- Complete with suction hose and accessories
- Automatic suction shut off system when the collection tank is full of liquids (for Wet & Dry models)
- Stainless steel Drain valve assembly for easy emptying (for Wet & Dry models)
- Quiet operation with only 72 dB

**Filtration System:**

- Washable, reusable main filter for dust and solids
- **HEPA<sup>Plus</sup>\*** Filtration with an efficiency of 99.995% @ 0.2 micron. Testing Method: IEST RP-CC034.3. H14. MIL-STD 282 / A.S.T.M. - D2986-91. MPPS method EN 1822.

**Applications:**

- Debris
- Dust
- Machine shops
- Maintenance/House keeping
- Metal Chips

**Specifications:**

Model	AV1-55 HEPA	AV2-55 HEPA
Air Flow (CFM)	120	230
Vacuum Pressure (H2O)	200	200
Collection Type	Dry	Dry
Capacity (gal)	10 or 15	10 or 15
dB(A) @ 6 ft	72 dB	72 dB
Air Line Size (I.D.)	0.5"	0.75"
Input Pressure (PSI)	80 to 100	100
Input Air Flow (CFM)	35	70

**\*\*Optional 3/8" (9.5 mm) I.D. Air Line Configuration Also Available\*\***

**Included Accessories:**

- Suction hose assembly
- Air Suction hose assembly
- Floor tool
- Crevice tool

**Optional Accessories:**

- Extension wand
- Single bend wand
- Flat tool
- Round Brush
- Wall brush

**Filtration Options:**

- **ULPA** Filtration with an efficiency of 99.9995% @ 0.12 micron. Testing Method: IEST RP-CC034.3. H15. MIL-STD 282 / A.S.T.M. - D2986-91. MPPS method EN 1822.
- Activated Carbon Filtration System to adsorb and neutralize fumes and vapors

If you have a special application or specific requirement, please feel free to contact us. As manufacturers, we can modify our units to meet your specific needs.

Hepa Vacuums, AIR OPERATED