

EV-10/15 RCT MC Electric Mercury Collection Vacuums



Industrial Vacuums for Hazardous Materials

Industrial Electrical Vacuums for Mercury collection

PrestiVac Mercury Vacuums are specifically designed to safely vacuum mercury spills and other products contaminated with Mercury. The **Mersob**® Brand Activated Carbon Filtration System adsorbs the harmful, toxic Mercury vapours and fumes generated. **HEPA^{Plus}*** absolute filtration at 99.995% @ 0.2 micron captures any contaminated particles. This combined filtration system provides a safe and clean working environment for the operator.

Features:

- Powerful Motor - High Performance
- Stainless steel construction makes it a solid unit that is easy to clean and sterilize
- Automatic Filter Shaker

- Mercury Collection System
- Complete with suction hose and accessories
- Automatic suction shut off system when the collection tank is full of liquids (for Wet & Dry models)
- Stainless steel Drain valve assembly for easy emptying (for Wet & Dry models)
- RCT Removable Collection Tank system makes it easy to empty and clean
- Stainless steel storage bin for hose and accessories
- Quiet operation with only xx dB

Filtration System:

- 5-stage Filtration System for maximum performance and efficiency
- Washable Filter
- Collection Filter Bag
- **HEPA^{Plus}** Filtration with an efficiency of 99.995% @ 0.2 micron. Testing Method: IEST RP-CC034.3. H14. MIL-STD 282 / A.S.T.M. - D2986-91. MPPS method EN 1822
- **Mersob**® Brand Activated Carbon Filtration System to adsorb harmful, toxic Mercury vapours/fumes

Applications:

- Mercury spills
- Mercury Decontamination

Industries:

- Chemical
- Hospitals
- Laboratories
- Manufacturing
- Medical labs
- Metal Working
- Mining
- Oil Refinery
- Shipboard

Specifications:

Model	EV1-10/15 RCT MC	EV2-10/15 RCT MC	EV1-10/15 RCT MC WD	EV2-10/15 RCT MC WD
Air Watts	561	652	529	626
Electricity	120v / 12a / 1488w	120v / 15a / 1790w	120v / 13a / 1528w	120v / 18a / 2102w
Air Flow (CFM)	123	202	113	191
Vacuum Pressure (H2O)	135	99	134	92
Collection Type	Dry	Dry	Wet & Dry	Wet & Dry
Capacity (gal)	10 or 15	10 or 15	10 or 15	10 or 15
dB(A) @ 6 ft				

Included Accessories:

- Suction hose assembly
- Stainless steel double bend wand assembly
- Floor tool
- Crevice tool

Optional Accessories:

- Extension wand
- Single bend wand
- Flat tool
- Round brush
- Wall brush

Options:

- Mercury Air Analyser

Filtration Options:

- Downstream **HEPA^{Plus}** Filtration with an efficiency of 99.995% @ 0.2 micron. Testing Method: IEST RP-CC034.3. H14. MIL-STD 282 / A.S.T.M. - D2986-91. MPPS method EN 1822

If you have a special application or specific requirement, please feel free to contact us. As manufacturers, we can modify our units to meet your specific needs.

Mercury, ELECTRIC