

## **EV-10/15 RCT MC Electric Mercury Collection Vacuums**



Industrial Vacuums for Hazardous Materials

Industrial Electrical Vacuums for Mercury collection

PrestiVac Mercury Vacuums are specifically designed to safely vacuum mercury spills and other products contaminated with Mercury. The **Mersob**® Brand Activated Carbon Filtration System adsorbs the harmful, toxic Mercury vapours and fumes generated. **HEPA<sup>Plus</sup>\*** absolute filtration at 99.995% @ 0.2 micron captures any contaminated particles. This combined filtration system provides a safe and clean working environment for the operator.

Features:

- Powerful Motor - High Performance
- Stainless steel construction makes it a solid unit that is easy to clean and sterilize
- Automatic Filter Shaker

- Mercury Collection System
- Complete with suction hose and accessories
- Automatic suction shut off system when the collection tank is full of liquids (for Wet & Dry models)
- Stainless steel Drain valve assembly for easy emptying (for Wet & Dry models)
- RCT Removable Collection Tank system makes it easy to empty and clean
- Stainless steel storage bin for hose and accessories
- Quiet operation with only xx dB

**Filtration System:**

- 5-stage Filtration System for maximum performance and efficiency
- Washable Filter
- Collection Filter Bag
- **HEPA<sup>Plus</sup>** Filtration with an efficiency of 99.995% @ 0.2 micron. Testing Method: IEST RP-CC034.3. H14. MIL-STD 282 / A.S.T.M. - D2986-91. MPPS method EN 1822
- **Mersob®** Brand Activated Carbon Filtration System to adsorb harmful, toxic Mercury vapours/fumes

**Applications:**

- Mercury spills
- Mercury Decontamination

**Industries:**

- Chemical
- Hospitals
- Laboratories
- Manufacturing
- Medical labs
- Metal Working
- Mining
- Oil Refinery
- Shipboard

**Specifications:**

Model	EV1-10/15 RCT MC	EV2-10/15 RCT MC	EV1-10/15 RCT MC WD	EV2-10/15 RCT MC WD
Air Watts	561	652	529	626
Electricity	120v / 12a / 1488w	120v / 15a / 1790w	120v / 13a / 1528w	120v / 18a / 2102w
Air Flow (CFM)	123	202	113	191
Vacuum Pressure (H2O)	135	99	134	92
Collection Type	Dry	Dry	Wet & Dry	Wet & Dry
Capacity (gal)	10 or 15	10 or 15	10 or 15	10 or 15
dB(A) @ 6 ft				

**Included Accessories:**

- Suction hose assembly
- Stainless steel double bend wand assembly
- Floor tool
- Crevice tool

Optional Accessories:

- Extension wand
- Single bend wand
- Flat tool
- Round brush
- Wall brush

Options:

- Mercury Air Analyser

Filtration Options:

- Downstream **HEPA<sup>Plus</sup>** Filtration with an efficiency of 99.995% @ 0.2 micron. Testing Method: IEST RP-CC034.3. H14. MIL-STD 282 / A.S.T.M. - D2986-91. MPPS method EN 1822

If you have a special application or specific requirement, please feel free to contact us. As manufacturers, we can modify our units to meet your specific needs.

Mercury, ELECTRIC